



1601030LFA Hidden Folding Stool
Mechanism Instruction


Version	A. 0
date	2019. 04. 09



seat panel size
clear cabinet distance +
side panel thickness




size drawing of panel



C panel size

Instruction:

1. seat panel weight + panel weight+C panel weight \leq 4.5kg
(if adopt 18mm panel, recommend panel width=410mm)
2. The descent speed will increase if the total weight(seat panel+panel+C panel) $>$ 4.5kg
4. Please inform us your total weight (includes seat panel+panel+C panel) when you place order, and we will equip with corresponding accessories.



size drawing of cabinet
(diagonal line of cabinet must be equal)

